

Handheld Copper Alloy Spectrometer



Overview

This rugged 245x250x90mm portable spectrometer delivers fast, precise elemental identification in the field. The 50kV X-ray tube and high sensitivity Si-PIN diode detector provide accurate analysis of metal alloys, impurities, and more. They deliver reliable results within seconds—without the need for laboratory testing. With dimensions of 245mm * 250mm * 90mm and weighing just 1.5 kg, it's equipped with a high-sensitivity Si-pin/SDD probe, targeting materials like Ag, W, and Ta with. Handheld / portable X-ray fluorescent (XRF) analyzers have the capability to non-destructively quantify or qualify nearly any element from Magnesium to Uranium, depending on the instrument configuration. Handheld XRF analyzers enable testing, identification, and verification on the go across crucial industries, including mining, construction. Revolutionize your on-the-spot elemental testing with the Spectro xSORT XHH04, a rugged and high-performance handheld ED-XRF spectrometer built for demanding industrial environments—from scrapyards and foundries to manufacturing and environmental screening. Why Choose the Spectro xSORT XHH04?

The X-MET8000 range of handheld X-ray fluorescence analyzers delivers the performance needed for rapid alloy grade identification and accurate chemistry of a wide variety of materials (solid and powder metals, polymers, wood, solutions, soil, ores, minerals etc). The X-MET handheld XRF analyzer.



Article Content

Applications Of Terras XRF Analyzer In The Alloy Field

Conclusion Handheld XRF spectrometers are powerful, portable, and effective tools for testing metal alloys. Their ability to provide fast, accurate, non-destructive analysis makes them an invaluable

Handheld/Portable XRF Analyzers for Precise Elemental Analysis

SPECTRO handheld and portable XRF analyzers are rugged, easy-to-use instruments designed for fast, accurate elemental analysis directly at your testing location. They deliver reliable results within

Vanta Handheld XRF Analyzer | Evident | Evident

Instantly identify materials and their chemical composition from any location using the Vanta handheld XRF analyzer. The Vanta series delivers fast, accurate

XRF Metal Analyzer: Quick results | Alloytester

A handheld Bruker metal analyzer is a robust, easy-to-use instrument for metal identification. Our metal analyzer can determine the composition and grades of

Handheld XRF Analyzer – SPECTRO xSORT XHH04

This provides ultra-wide coverage of elements and alloys, allowing users to test samples of varying sizes without the need to switch methods. Whether in the

Handheld XRF Spectrometers for Elemental Analysis | Bruker

Alloy verification is fast and seamless using Bruker's handheld XRF analyzers. Alloy-specific calibrations and a state-of-the-art XRF engine support rapid confident alloy grade identification on the factory floor.

Quantitative analysis of copper alloys by means of portable X-ray ...

Portable XRF is one of the techniques most widely used for non-invasive analysis of ancient copper alloys. One of its limitations is that the presence of inhomogeneities on the surface

Handheld Alloy Analyzer | China Handheld Alloy

EXPLORER 5000 hand-held X-ray fluorescence spectrometer is an important analytical testing tool, which can conduct precise chemical composition analysis

XRF Metal Analyzer

Alloys That Can Be Detected During Scrap Metal Identification X-ray spectrometer analysis will detect and identify all steels, as well as the following alloy bases:

Metal Spectrometer | Spectrometer | Portable Metal

Portable Metal Spectrometer is used for inspection, quality control, and alloy identification. Many times this is also called a metal spectrometer and PMI

Contact Us

For more information, pricing, or custom solutions, please contact us:

Website: <https://www.umele-pestovani.eu>

Email: info@umele-pestovani.eu

Phone: +49 152 287 6349

Address: Neue Mainzer Straße 66-68, 60311 Frankfurt am Main, Germany

This document is for informational purposes only. Specifications subject to change without notice.

